



Ref. Certif. No.

US-35724-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Accessory, Power Distribution Unit - Single and Poly phase, for use in certified ITE.

Name and address of the applicant

SCHNEIDER ELECTRIC IT CORPORATION,
FKA APC AMERICAN POWER CONVERSION
132 FAIRGROUNDS RD
PO BOX 278
WEST KINGSTON RI 02892 USA

Name and address of the manufacturer

SCHNEIDER ELECTRIC IT CORPORATION,
FKA APC AMERICAN POWER CONVERSION
132 FAIRGROUNDS RD
PO BOX 278
WEST KINGSTON RI 02892 USA

Name and address of the factory

Note: When more than one factory, please report on page 2

EAST INDIA TECHNOLOGIES PVT. LTD.
SURVEY NO. 17, KAMMANAHALLI VILLAGE BANNERGHATTA
RD BANGALORE KARNATAKA 560076
INDIA

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)

APC by Schneider Electric



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

APDU9959EU3, APDU9981EU3, APDU9953,
APDU9941 (PSE/JAPAN CB only)

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014 / A11:2017;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E177299-A6006-CB-1 issued on 2020-05-04

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-05-04

Signature:

Jolanta M. Wroblewska

For full legal entity names see www.ul.com/ncbnames



Ref. Certif. No.

US-35724-UL

Factories:

SCHNEIDER ELECTRIC IT BUSINESS INDIA PVT LTD
PLOT NO 73 SURVEY NO. 103, 2ND PHASE JIGANI INDUSTRIAL AREA BANGALORE KARNATAKA 562106
INDIA

Ratings:

APDU9953:

INPUT: 200-240VAC; 50/60Hz; 32A
OUTPUT: 200-240VAC; 16A MAX PER BANK; 32A TOTAL
C19: 16A MAX PER OUTLET
C13: 10A MAX PER OUTLET

APDU9959EU3

INPUT: 220-240VAC; 50/60Hz; 16A
OUTPUT : 220-240VAC; 16A TOTAL
C19: 16A MAX PER OUTLET
C13: 10A MAX PER OUTLET

APDU9981EU3:

INPUT: 220/380-240/415VAC; 3W+N+PE; 50/60Hz; 16A
OUTPUT: 220-240VAC, 16A PER PHASE; 16A PER BANK
C19: 16A MAX PER OUTLET
C13: 10A MAX PER OUTLET

APDU9941: (PSE/JAPAN CB Only)

INPUT: 200-240/208 VAC, 50/60Hz; 24A
OUTPUT: 200-240/208 VAC, 16A PER BANK; 24A TOTAL
C21: 20A MAX (PSE) PER OUTLET
C15: 15A MAX (PSE) PER OUTLET

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-05-04

Signature:

Jolanta M. Wroblewska