


Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**RE22R2MWMR**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

Max. Switching Current: 8A  
 Max. Switching Voltage: 250 V  
 Max. Power Consumption: 3VA (AC), 1.5W (DC)  
 Input Signals: Y1 - Control Signal, X1 - Pause Signal, Z1 - Ext Potentiometer  
 Function Available: W, Wt  
 Function Description: Interval relay  
 Time Ranges: 0.05 s to 300 h  
 Type of Output: Relay  
 Contact Configuration: DPDT

Description: Timer, 24-240 VAC/VDC Input, 8A DPDT Relay Output, Interval  
 Ambient Storage Temp.: -40 to +70 °C (-40 to +158 °F)  
 Ambient Operating Temp.: -20 to +60 °C (-4 to +140 °F)  
 Degree of Protection Term. Block: IP20  
 Degree of Protection Housing: IP40  
 Electrical Life @ Rated Load: 100,000 cycles  
 Mechanical Life @ Rated Load: 20,000,000 cycles  
 Dial Settings: Range = 1s to 300h, Time setting = 1 to 10, R2 = Timed, Inst  
 Mounting: 35 mm DIN Rail