



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**SC300A400LCFP**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Sensing Window:	
Far Limit:	101.6 mm (4.0 in)
Sensing Range:	
Circuit Type:	Discrete
Output Mode:	DC
Volts Type:	12-24 VDC
Voltage Range:	100 mA
Max Load:	25 mA
Current Consumption:	500 kHz
Sonic Frequency:	-30° to 70° C (-22° to 158° F)
Temp Range:	4X (indoor use only)
NEMA Type:	IP67
IP Rating:	UL, CE Rohs
Standards:	

**Specification:**

Sensor Type:	Ultrasonic Sensor
Description:	Ultrasonic Sensor, Discrete, Flat Profile, 12-24 VDC
Body Style:	Flat Profile
Diameter:	
Housing Material:	0
Face Material:	Glass Epoxy
Field Configurable:	Yes, using AC441 Configurator and Superprox+ Software
Functionality:	Configurable
Cable Size:	3.0 m (10 ft)
Connector Type:	
Special Features:	Label on Cable