

Product data sheet

Characteristics

VLS1P063R1E

Disconnect switch, TeSys VLS, additional pole, early-make closing, 63A, for 63A switch, size 1, DIN rail

Product availability: Non-Stock - Not normally stocked in distribution facility



Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Range	TeSys
Device short name	VLS1P
Product or Component Type	Additional pole
Performance level	High performance
Poles description	1P
Contacts type and composition	1 NO
Contact operation	Early make
Range compatibility	TeSys TeSys VARIO LS VLS3P
Network type	AC
Network Frequency	50/60 Hz
Suitability for isolation	Yes

Complementary

Mounting Location	Right Left
Mounting Support	DIN rail
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 KV
[Ith] conventional free air thermal current	63 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	45 A
[Ie] rated operational current	60 A Ue: 600 V UL 508 63 A AC-21A Ue: 400 V 63 A AC-21A Ue: 500 V 63 A AC-21A Ue: 690 V 45 A AC-22A Ue: 400 V 45 A AC-22A Ue: 500 V 45 A AC-22A Ue: 690 V 45 A AC-23A Ue: 400 V 25 A AC-23A Ue: 500 V 25 A AC-23A Ue: 690 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rated operational power in W	22 KW 400 V AC-23A) 22 KW 500 V AC-23A) 22 KW 690 V AC-23A)
Intermittent duty class	Class 120 - 60 %
Making capacity	120 A 690 V AC-22A 400 A 690 V AC-23A 94.5 A 690 V AC-21A
[Icm] rated short-circuit making capacity	1128 A 690 V
[Icw] rated short-time withstand current	800 A 690 V 1 s
Rated conditional short-circuit current	50 KA 400 V 63 A gG
Breaking capacity	120 A 690 V AC-22A) 320 A 690 V AC-23A) 94.5 A 690 V AC-21A)
Mechanical durability	100000 Cycles
Electrical durability	15000 Cycles AC-21
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.02 in ² (16 mm ²) flexible - without cable end
Tightening torque	Power circuit 15.93...17.70 lbf.in (1.8...2 N.m) screw clamp terminals
Height	3.07 In (78 mm)
Width	0.47 In (12 mm)
Depth	1.72 In (43.6 mm)
Net Weight	0.09 Lb(US) (0.04 kg)
Color	Gray

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481205438
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 In (3.3 cm)
Package 1 Width	3.50 In (8.89 cm)
Package 1 Length	3.00 In (7.62 cm)
Package 1 Weight	0.11 Lb(US) (0.05 kg)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 In (15 cm)
Package 2 Width	5.91 In (15 cm)
Package 2 Length	15.75 In (40 cm)
Package 2 Weight	3.34 Lb(US) (1.515 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Product Life Status : **End of commercialisation**