



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**SM350A20800**



**Telemecanique**  
Sensors

Telemecanique Sensors  
1875 Founders Drive  
Dayton, OH 45420-4017  
Customer Care Center : 1-800-435-2121  
Web : www.tesensors.com

**Technical Information:**

Sensing Window:	13.0 mm (0.5 in)
Far Limit:	50.8 mm (2.0 in)
Sensing Range:	
Circuit Type:	Normally Open
Output Mode:	NPN/PNP
Volts Type:	DC
Voltage Range:	12-24 VDC
Max Load:	100 mA
Current Consumption:	25 mA
Sonic Frequency:	500 kHz
Temp Range:	-30° to 70° C (-22° to 158° F)
NEMA Type:	4X (indoor use only)
IP Rating:	IP67
Standards:	UL, CE Rohs

**Specification:**

Sensor Type:	Ultrasonic Sensor
Description:	Ultrasonic Sensor, Discrete, 12 mm Barrel, 12-24 VDC
Body Style:	Barrel
Diameter:	12 mm
Housing Material:	0
Face Material:	Glass Epoxy
Field Configurable:	No
Functionality:	Standard On/Off
Cable Size:	
Connector Type:	M8 pico 4-pin
Special Features:	