



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

SM956A420000S



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Sensing Window:
Far Limit:
Sensing Range: 120.0 mm to 2.0 m (4.7 in to 79.0 in)
Circuit Type:
Output Mode: Inverse 4 to 20 mA
Volts Type: DC
Voltage Range: 15-24 VDC
Max Load: 10 - 500 ohm
Current Consumption: 80 mA
Sonic Frequency: 200 Hz
Temp Range: 0° to 50° C (32° to 122° F)
NEMA Type: 4X (indoor use only)
IP Rating: IP67
Standards: UL, CE Rohs

Specification:

Sensor Type: Ultrasonic Sensor
Description: Ultrasonic Sensor, Analog - Current (mA), 30 mm Barrel, 15-24 VDC
Body Style: Barrel
Diameter: mm
Housing Material: Silicone Rubber
Face Material: No
Field Configurable: Standard: No Foreground Or Background Suppression
Functionality: M12
Cable Size:
Connector Type:
Special Features: