

Product data sheet

Characteristics

VLS3P125D2

Disconnect switch, TeSys VLS, body switch, 125A, 60HP at 480VAC, UL98, three phase, 50kA SCCR, size 2, door mount

Product availability: Stock - Normally stocked in distribution facility

Price*: 220.07 USD

Main

Range	TeSys
Product name	TeSys VARIO LS
Device short name	VLS3P
Product or Component Type	Switch body

Complementary

Mounting Support	Door
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Color	Gray
[Ue] rated operational voltage	600 V AC 50/60 Hz UL 508
Network type	AC
Network Frequency	50/60 Hz
Maximum Horse Power Rating	30 Hp 200/208 V AC 30 Hp 240 V AC 60 Hp 480 V AC 60 Hp 600 V AC 7.5 Hp 120 V AC 10 Hp 240 V AC
[Ue] rated operational voltage	690 V AC 50/60 Hz
Rated operational power in W	55 KW 400 V AC-23A) 45 KW 500 V AC-23A) 45 KW 690 V AC-23A)
[Ie] rated operational current	100 A Ue: 600 V UL98 125 A AC-21A Ue: 400 V 125 A AC-21A Ue: 500 V 125 A AC-21A Ue: 690 V 125 A AC-22A Ue: 400 V 125 A AC-22A Ue: 500 V 125 A AC-22A Ue: 690 V 125 A AC-23A Ue: 400 V 100 A AC-23A Ue: 500 V 47 A AC-23A Ue: 690 V

[Ith] conventional free air thermal current	125 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	100 A
Making capacity	1250 A 690 V AC-23A 187.5 A 690 V AC-21A 375 A 690 V AC-22A
Breaking capacity	187.5 A 690 V AC-21A) 375 A 690 V AC-22A) 1000 A 690 V AC-23A)
Product compatibility	Fuse J 100 A maximum: 50 kA at 600 V AC
Rated conditional short-circuit current	50 KA 400 V 125 A gG
[Icm] rated short-circuit making capacity	3550 A 690 V
Intermittent duty class	Class 120 - 60 %
[Uimp] rated impulse withstand voltage	8 KV
[Icw] rated short-time withstand current	2500 A 690 V 1 s
Mechanical durability	30000 Cycles
Electrical durability	30000 Cycles AC-21
AWG gauge	AWG 12...AWG 1 copper
Connections - terminals	Power circuit screw clamp terminals 0.08 in ² (50 mm ²) solid Power circuit screw clamp terminals 0.1 in ² (70 mm ²) flexible - without cable end
Tightening torque	Power circuit 44.3...53.1 lbf.in (5...6 N.m) screw clamp terminals
Height	2.8 In (70 mm)
Width	2.8 In (70 mm)
Depth	3.9 In (100 mm)
Product Weight	0.805 Lb(US) (0.365 kg)

Environment

Standards	UL98 CSA C22.2 No 4 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	OCP1
GTIN	3606481156587
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.150 In (8.000 cm)
Package 1 Width	3.346 In (8.500 cm)
Package 1 Length	4.921 In (12.500 cm)
Package 1 Weight	15.273 Oz (433.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	11.811 In (30.000 cm)
Package 2 Width	11.811 In (30.000 cm)

Package 2 Length	15.748 In (40.000 cm)
Package 2 Weight	26.848 Lb(US) (12.178 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Product Life Status :	Commercialised
-----------------------	-----------------------