



Overview

Model Name	APC Smart-UPS 1500VA LCD 230V with SmartConnect
Includes	CD with software , Cat 5 ethernet cable , Documentation CD , Installation guide , USB cable
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Afghanistan , Albania , Andorra , Australia , Austria , Bahrain , Belgium , Bosnia And Herzegovina , Botswana , Brunei Darussalam , Bulgaria , Cambodia , Croatia , Cyprus , Czech Republic , Denmark , East Timor , Egypt , Estonia , Fiji , Finland , France , Germany , Ghana , Greece , Hong Kong , Hungary , Iceland , Indonesia , Ireland , Israel , Italy , KOREA, REPUBLIC OF , Kuwait , Latvia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Malta , Moldova, Republic Of , Mongolia , Mozambique , Netherlands , New Zealand , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Philippines , Poland , Portugal , Romania , Saudi Arabia , Singapore , Slovakia (Slovak Republic) , Slovenia , South Africa , Spain , Sweden , Switzerland , Thailand , United Arab Emirates , Viet Nam , Zimbabwe

Output

Output Power Capacity	1000 Watts / 1500 VA
Max Configurable Power (Watts)	1000 Watts / 1500 VA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	220, 240V
	Line Interactive
Waveform Type	Sine wave
Output Connections	(2) IEC Jumpers (Battery Backup) , (8) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C14
Cord Length	1.83 meters
Input voltage range for main operations	160 - 286 V
Input voltage adjustable range for mains operation	151 - 302V
Other Input Voltages	220 , 240

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	RBC7
RBC Quantity	1

Communications & Management

Interface Port(s)	SmartSlot , USB
Available SmartSlot™ Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
Emergency Power Off (EPO)	--

Surge Protection and Filtering

Surge energy rating	459 joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	219.0 mm
Maximum Width	171.0 mm
Maximum Depth	439.0 mm
Net Weight	24.09 kg
Shipping Weight	27.23 kg
Shipping Height	376.0 mm
Shipping Width	328.0 mm
Shipping Depth	595.0 mm
Color	Black
Units per Pallet	12.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB
Online Thermal Dissipation	135.000 BTU/hr

Conformance

Approvals	CE , CSA , EAC , EN/IEC 62040-1 , EN/IEC 62040-2 , RCM , UL 1778 , VDE
Standard warranty	3 years repair or replace (excluding battery) and 2 year for battery

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs