



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
VM18CAQ


 Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Sensing Window:
 Far Limit:
Sensing Range: 50.8 to 508 mm (2.0 to 20.0 in)
Circuit Type:
Output Mode: Autoslope 4 to 20 mA
Volts Type: DC
Voltage Range: 15-24 VDC
Max Load: 10 - 350 ohm
Current Consumption: 40 mA
Sonic Frequency: 300 Hz
Temp Range: -30° to 70° C (-22° to 158° F)
NEMA Type: 4X (indoor use only)
IP Rating: IP67
Standards: UL, CE Rohs

Specification:

Sensor Type: Ultrasonic Sensor
Description: Ultrasonic Sensor, Analog - Current (mA), 18 mm Barrel, 15-24 VDC
Body Style: Barrel
Diameter: mm
Housing Material:
Face Material: Glass Epoxy
Field Configurable: No
Functionality:
Cable Size:
Connector Type: M12
Special Features: Tamper Proof with PB100 Pushbutton Accessory