



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

General

Provided equipment	CD with software Communication cable Documentation CD Installation guide Removable support feet USB cable Warranty card
Additional specification	Lithium-Ion
Number of tare power	25 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	S

Physical

Number of rack unit	3U
Colour	Black
Depth	59 Cm
Height	12.8 Cm
Mounting position	Vertical
Mounting preference	No preference
Product weight	30.53 Kg
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Width	43.2 Cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Input

Network frequency	40...70 Hz auto-sensing
Plug standard	IEC 60320 C14
Input voltage limits	50...150 V 40% load 80...150 V
Input voltage	220 V 240 V
Input voltage	230 V

Output

Rated power in W	900 W
Maximum configurable power in W	900 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Output voltage	220 V 240 V
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Nb of power socket outlets	8 IEC 60320 C13
Bypass type	Built-in bypass
Graph display	1
Output voltage	230 V
Maximum configurable power in VA	1000 VA
Rated power in VA	1000 VA

Conformance

Product certifications	CE EAC RCM VDE
Marking	CE Mark

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0.00...15240.00 M
Acoustic level	50 dBA
Heat dissipation	400 Btu/H
Show note OP temperature	No
IP degree of protection	IP20

Batteries & Runtime

Battery type	Li-Ion (Lithium-Ion)
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	6 H
Liquid value	0
Battery voltage	48 V
Battery curve	L1
Battery charger power	103 W rated
Battery power in VAH	585 VAh capacity 622 VAh runtime

Battery life	5...10 Year(S)
Battery option	XBP48RM1U-LI 1 1243 VAh XBP48RM1U-LI 2 1865 VAh XBP48RM1U-LI 3 2486 VAh XBP48RM1U-LI 4 3108 VAh
Extended runtime	1

Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes

Surge Protection and Filtering

Surge energy rate	340 J
-------------------	-------

Packing Units

Package 1 Weight	46.86 Kg
Package 1 Height	44.5 Cm
Package 1 width	60 Cm
Package 1 Length	85 Cm
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Product Life Status :	Commercialised
-----------------------	-----------------------