



Runtime estimates for Easy UPS SRVSPM3KRIL, Extended Runtime

Load Power (W) / % of Battery Power	0 W	100 W	200 W	300 W	400 W	500 W
SRVSPM3KRIL	0	0	0	0	0	0
SRVSPM3KRIL - (3) SRVSP3BL3P-6A	2 h 45 min	1 h 18 min	27 min 20 sec	17 min 10 sec	12 min 44 sec	
SRVSPM3KRIL - (3) SRVSP3BL3P-6A	3 h 35 min	2 h 07 min	1 h 18 min	10 min	8 min	
SRVSPM3KRIL - (3) SRVSP3BL3P-6A	3 h 54 min	4 h 20 min	1 h 37 min	1 h 4 min	48 min	
SRVSPM3KRIL - (3) SRVSP3BL3P-6A	4 h 18 min	6 h 8 min	2 h 10 min	1 h 20 min	1 h 8 min	
SRVSPM3KRIL - (3) SRVSP3BL3P-6A	10 h 30 min	15 h 30 min	2 h 52 min	1 h 24 min	1 h 20 min	

Overview

Presentation	For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Product or component type	Uninterruptible power supply (UPS)
Input voltage	220 V 240 V
Output voltage	230 V
Output voltage	220 V 240 V
Rated power in W	2400 W
Rated power in VA	3000 VA
Input Connection Type	IEC 60320 C20
Output connection type	6 IEC 60320 C13 1 IEC 60320 C19
Number of rack unit	2U
Number of cables	1
Provided equipment	1 IEC 60320 C19 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable 1 battery cable 1 rack mounting brackets user manual

Batteries & Runtime

Battery type	External battery system
Battery voltage	72 V
Extended runtime	1
Number of battery filled slots	0
Number of battery free slots	0
Battery charger power	350 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	8.6 Cm
Width	43.8 Cm
Depth	46.2 Cm
Net weight	9.5 Kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
USB compatible	Yes
Mounting position	Horizontal

Input

Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	3000 VA
Maximum configurable power in W	2400 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE[RETURN]UKCA
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 M
Acoustic level	50 dBA
IP degree of protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
Free slots	1
Control panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 Cm
Package 1 Width	55.4 Cm
Package 1 Length	70 Cm
Package 1 Weight	13.671 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	8
Package 2 Height	115 Cm
Package 2 Width	80 Cm
Package 2 Length	120 Cm
Package 2 Weight	124 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**