

Product data sheet


Characteristics

VLS3P063D2

Disconnect switch, TeSys VLS, body switch, 60A, 40HP at 480VAC, UL98, three phase, 50kA SCCR, size 2, door mount

Product availability: Stock - Normally stocked in distribution facility

Price*: 127.21 USD



Main

Range	TeSys
Product name	TeSys VARIO LS
Device short name	VLS3P
Product or Component Type	Switch body

Complementary

Mounting Support	Door
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Color	Gray
[Ue] rated operational voltage	600 V AC 50/60 Hz UL 508
Network type	AC
Network Frequency	50/60 Hz
Maximum Horse Power Rating	20 Hp 200/208 V AC 20 Hp 240 V AC 40 Hp 480 V AC 40 Hp 600 V AC 3 Hp 120 V AC 7.5 Hp 240 V AC
[Ue] rated operational voltage	690 V AC 50/60 Hz
Rated operational power in W	30 KW 400 V AC-23A) 45 KW 500 V AC-23A) 45 KW 690 V AC-23A)
[Ie] rated operational current	60 A Ue: 600 V UL98 63 A AC-21A Ue: 400 V 63 A AC-21A Ue: 500 V 63 A AC-21A Ue: 690 V 63 A AC-22A Ue: 400 V 63 A AC-22A Ue: 500 V 63 A AC-22A Ue: 690 V 63 A AC-23A Ue: 400 V 63 A AC-23A Ue: 500 V 47 A AC-23A Ue: 690 V

[Ith] conventional free air thermal current	63 A (at 131 °F (55 °C))
[Ithe] conventional enclosed thermal current	63 A
Making capacity	630 A 690 V AC-23A 94.5 A 690 V AC-21A 189 A 690 V AC-22A
Breaking capacity	94.5 A 690 V AC-21A) 189 A 690 V AC-22A) 504 A 690 V AC-23A)
Product compatibility	Fuse J 60 A maximum: 50 kA at 600 V AC
Rated conditional short-circuit current	50 KA 400 V 63 A gG
[Icm] rated short-circuit making capacity	3550 A 690 V
Intermittent duty class	Class 120 - 60 %
[Uimp] rated impulse withstand voltage	8 KV
[Icw] rated short-time withstand current	2500 A 690 V 1 s
Mechanical durability	30000 Cycles
Electrical durability	30000 Cycles AC-21
AWG gauge	AWG 12...AWG 1 copper
Connections - terminals	Power circuit screw clamp terminals 0.08 in ² (50 mm ²) solid Power circuit screw clamp terminals 0.1 in ² (70 mm ²) flexible - without cable end
Tightening torque	Power circuit 44.3...53.1 lbf.in (5...6 N.m) screw clamp terminals
Height	2.8 In (70 mm)
Width	2.8 In (70 mm)
Depth	3.9 In (100 mm)
Net Weight	0.805 Lb(US) (0.365 kg)

Environment

Standards	UL98 CSA C22.2 No 4 IEC 60947-3
Product Certifications	cULus[RETURN]GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	US10CP121734
Discount Schedule	OCP1
GTIN	3606481156556
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.150 In (8.000 cm)
Package 1 Width	3.346 In (8.500 cm)
Package 1 Length	4.724 In (12.000 cm)
Package 1 Weight	15.309 Oz (434.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	11.811 In (30.000 cm)
Package 2 Width	11.811 In (30.000 cm)

Package 2 Length	15.748 In (40.000 cm)
Package 2 Weight	26.980 Lb(US) (12.238 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Product Life Status :	Commercialised
-----------------------	-----------------------