


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

XB5EVB5



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Supply Voltage (Input): 24VAC/DC, 50/60 Hz
 Supply Voltage Limits: 21.6-26.4 VAC 19.2-30 VDC
 Current Rating: 18mA
 Surge Withstand: 1 kV conforming to IEC 61000-4-5
 Bulb Type: Protected and Integrated LED
 Ambient Air Temp. (for storage): -40°C to 70°C
 Ambient Air Temp. (for operation): -25°C to 70°C
 Conformity to Standards: EN/IEC 60947-1, EN/IEC 60947-5-1, UL508, CSA C22-2 n°14, IEC 61000-4-2, IEC 61000-4-3, IEC 6100-4-4, UL, FCC, CSA, CE

Specification:

Description: 22mm Monolithic Pilot light, complete, 24V, Orange
 Vibration Resistance: 5 gn (f=12...500 Hz) conforming to IEC 60068-2-6
 Shock Resistance: 33 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27, 50 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27
 IK degree of Protection: IK05 conforming to IEC 50102
 Degree of Protection: IP66 conforming to IEC 60529, NEMA 4X, NEMA 13
 Electric Service Life: 100,000 hours at rated voltage and at 25°C