



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

VM18PNOQ



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Sensing Window:
Far Limit:
Sensing Range: 50.8 to 508 mm (2.0 to 20.0 in)
Circuit Type: Normally Open
Output Mode: PNP
Volts Type: DC
Voltage Range: 12-24 VDC
Max Load: 100 mA
Current Consumption: 40 mA
Sonic Frequency: 300 Hz
Temp Range: -30° to 70° C (-22° to 158° F)
NEMA Type: 4X (indoor use only)
IP Rating: IP67
Standards: UL, CE Rohs

Specification:

Sensor Type: Ultrasonic Sensor
Description: Ultrasonic Sensor, Discrete, 18 mm Barrel, 12-24 VDC
Body Style: Barrel
Diameter: mm
Housing Material: Glass Epoxy
Face Material: No
Field Configurable: No
Functionality:
Cable Size:
Connector Type: M12
Special Features: Tamper Proof with PB100 Pushbutton Accessory