



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**VM18PPO0000Q**



**Telemecanique**  
Sensors

Telemecanique Sensors  
1875 Founders Drive  
Dayton, OH 45420-4017  
Customer Care Center : 1-800-435-2121  
Web : www.tesensors.com

**Technical Information:**

Sensing Window:  
Far Limit:  
Sensing Range: 50.8 to 508 mm (2.0 to 20.0 in)  
Circuit Type: Normally Open  
Output Mode: PNP  
Volts Type: DC  
Voltage Range: 12-24 VDC  
Max Load: 100 mA  
Current Consumption: 40 mA  
Sonic Frequency: 300 Hz  
Temp Range: -30° to 70° C (-22° to 158° F)  
NEMA Type: 4X (indoor use only)  
IP Rating: IP67  
Standards: UL, CE Rohs

**Specification:**

Sensor Type: Ultrasonic Sensor  
Description: Ultrasonic Sensor, Dual-Level - Pump-out Latch, 18 mm Barrel, 12-24 VDC  
Body Style: Barrel  
Diameter: mm  
Housing Material: Glass Epoxy  
Face Material: No  
Field Configurable: No  
Functionality:  
Cable Size:  
Connector Type: M12  
Special Features: Tamper Proof with PB100 Pushbutton Accessory