


Part No.:

XBTZGJBOX



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Technical Information:

North America Certifications: UL 508, CSA-C22.2, No. 142-M1987
 IEC, CE Certifications: EN 61131-2, IEC 61000-6-2, CE
 FCC & EMC: FCC (Class A), C-Tick
 Applicable Machine Safety Std.: IEC 62061: SIL CL 3; EN 954-1: Category 4, EN ISO 13849-1: (PL) PLe
 Marine Certifications:
 Other Certifications:
 Common Automation Protocols: Modbus, Uni-TE, Modbus TCP/IP, FIPWAY, FIPIO, Modbus Plus
 Other Protocols: PacDrive, Siemens, Omron, Mitsubishi, Rockwell
 Operating Temperature Range: 0c to 50c
 Storage Temperature Range: -20c to +60c
 Relative Humidity: 0 to 90% non condensing

Specification:

Description:
 Screen Type: N/A - See XBTGH2460
 Resolution: N/A - See XBTGH2460
 Interface Ports: SUB-D9 (RS 232C/RS 422/485 serial link)
 Ethernet Ports: RJ45 (10BASE-T/100BASE-TX)
 USB Ports: On XBTGH2460: Type A (V1.1)
 Operating System: Key switch, 3-pos enable, Oper key, E-stop, FO & F2 function key, Buzzer out
 Enclosure Rating: IP65, NEMA 4X
 Processor: N/A - See XBTGH2460
 SRAM: N/A - See XBTGH2460
 Storage: N/A - See XBTGH2460
 Supply Voltage: 24 VDC