


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XCKM102H7



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Terminal Type: Screw Clamp
 Enclosure Rating: NEMA 4/12; IP65
 Approvals: UL # E39281 - CSA # LR44087 Class 3211-03 - CE Marked
 Weight: 0.255 kg (0.562 lb)
 Conforming to Standards:
 RoHS: Yes
 Operating Temperature Range: -13 to 158 ° F
 Shock Resistance: 50G
 Vibration Resistance: 25G (10-500Hz)
 Max. Actuation Speed : 0.5 m/s
 Repeat Accuracy: 0.05 mm on the tripping points
 Operating Torque/Force: 106 Inch-Pounds (12Nm)

Specification:

Description: XCKM Limit Switch Steel roller plunger
 Body Style/Type Description: IEC OsiSense Limit Switches XCKM Compact SemiModular 64 mm Metal Body
 Head Type: ZCKD02 Steel top roller plunger
 Lever Arms:
 Body with Contact Type: ZCKM1H7 2-pole N.O./N.C. Snap Action
 Conduit Thread: 3 entries CM10
 Ampere Rating Continuous: 10A
 Maximum Voltage Rating: 240VAC/250VDC
 Actuation: Horizontal
 Actuator Action: Momentary
 Lever Arm Length:
 Roller Dimension:
 Roller Material: Steel
 Contact Configuration: 1 N.O./1 N.C.
 Contact Operation: Snap Action
 Connection Type: CM10 with #DE9RA1012 adapter for 0.5 Inch NPT
 Head Material: Plastic
 Positive Opening: Yes
 Cable Length: