


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

XCKP2102N12



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Terminal Type: Screw Clamp
 Enclosure Rating: NEMA 1/2/4/6/12/13; IP66/67
 Approvals: UL # E164353 - CSA #164581 - CE Marked
 Weight: 0.095 kg (0.209 lb)
 Conforming to Standards: CENELEC EN 50047
 RoHS: Yes
 Operating Temperature Range: -13 to 158 ° F
 Shock Resistance: 50G
 Vibration Resistance: 25G
 Max. Actuation Speed : 0.5 m/s
 Repeat Accuracy: 0.1 mm on the tripping points
 Operating Torque/Force: 106 Inch-Pounds (12Nm)

Specification:

Description: XCKP Limit Switch top roller plunger
 Body Style/Type Description: IEC OsiSense Compact Modular 31mm wide Plastic Limit Switches
 Head Type: ZCE02 Steel top roller plunger
 Lever Arms:
 Body with Contact Type: ZCP21 2-pole N.O. / N.C. Snap Action
 Conduit Thread: ZCPEN12 1/2" NPT
 Ampere Rating Continuous: 10A
 Maximum Voltage Rating: 240VAC/250VDC
 Actuation: Horizontal
 Actuator Action: Momentary
 Lever Arm Length:
 Roller Dimension: 11.6 x3.5mm
 Roller Material: Steel
 Contact Configuration: 1 N.O./1 N.C.
 Contact Operation: Snap Action
 Connection Type: Conduit Entrance (0.5 Inch NPT)
 Head Material: Zamak
 Positive Opening: Yes
 Cable Length: