


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**XCKP2910N12**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Terminal Type: Screw Clamp  
 Enclosure Rating: NEMA 1/2/4/6/12/13; IP66/67  
 Approvals: UL # E164353 - CSA #164581 - CE Marked  
 Weight: 0.090 kg (0.198 lb)  
 Conforming to Standards: CENELEC EN 50047  
 RoHS: Yes  
 Operating Temperature Range: -13 to 158 ° F  
 Shock Resistance: 50G  
 Vibration Resistance: 25G  
 Max. Actuation Speed : 0.5 m/s  
 Repeat Accuracy: 0.1 mm on the tripping points  
 Operating Torque/Force: 133 Inch-Pounds (15Nm)

**Specification:**

Description: XCKP Limit Switch metal end plunger  
 Body Style/Type Description: IEC OsiSense Compact Modular 31mm wide Plastic Limit Switches  
 Head Type: ZCE10 Metal end plunger  
 Lever Arms:  
 Body with Contact Type: ZCP29 2-pole N.C./N.C. Snap action  
 Conduit Thread: ZCPEN12 1/2" NPT  
 Ampere Rating Continuous: 10A  
 Maximum Voltage Rating: 240VAC/250VDC  
 Actuation: Vertical  
 Actuator Action: Momentary  
 Lever Arm Length:  
 Roller Dimension:  
 Roller Material:  
 Contact Configuration: 1 N.C./1 N.C.  
 Contact Operation: Snap Action  
 Connection Type: Conduit Entrance (0.5 Inch NPT)  
 Head Material: Zamak  
 Positive Opening: Yes  
 Cable Length: