



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**XSDC607139**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Detecting Distance: 30.0 - 60.0 mm (1.17 - 2.34 in)  
 Circuit Type: 2 wire  
 Output Mode: NO/NC  
 Volts Type: DC  
 Voltage Range: 12-48 VDC  
 Max Load: 100 mA  
 Shielding: Non shielded  
 Max Switching Frequency: 20 Hz  
 Temp Range: -25° to 70° C (-13° to 158° F)  
 NEMA Type: 4X (indoor use only)  
 IP Rating: IP67  
 Standards: UL, CE Rohs

**Specification:**

Sensor Type: Inductive  
 Description: Proximity Sensor, Inductive, Flat Profile, 12-48 VDC, Non shielded  
 Body Style: Flat Profile  
 Diameter:  
 Housing Material: Thermoplastic Polyester  
 Cable Size: 2.0 m (6.6 ft)  
 Connector Type:  
 Special Features: