



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XUDA2NSMM8



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Diffuse with Background Suppression:

Diffuse:
Polarized Retroreflective:
Thru Beam:
Retroreflective:
Circuit Type: NPN
Output Mode: Light/Dark Operate
Power: DC
Voltage Range: 12-24 VDC
Max Load: 100 mA
Max Switching Frequency : 1000 or 5000 Hz
Temp Range: -10° to 55° C (13° to 131° F)
NEMA Type: 4X (indoor use only)
IP Rating: 65
Standards: UL, CE Rohs

Specification:

Sensor Type: Fiber Amplifier
Description: Photoelectric, Fiber Amplifier, DIN-rail, 12-24 VDC
Body Style: DIN-rail
Diameter:
Housing Material: Plastic - PBT
Face Material: PMMA
Adjustment: Pushbutton fine teach
Cable Size:
Connector Type: 4-pin M8
Special Features: Hinged cover