


**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**XCKN2521P20**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Terminal Type: Screw Clamp  
 Enclosure Rating: NEMA 12, 4X Indoor; IP65  
 Approvals: UL # E164353 - CSA # 164581 - CE Marked  
 Weight: 0.070 kg (0.150 lb)  
 Conforming to Standards: CENELEC EN 50047  
 RoHS: Yes  
 Operating Temperature Range: -13 to 158 ° F  
 Shock Resistance: 50G  
 Vibration Resistance: 25G  
 Max. Actuation Speed : 1 m/s  
 Repeat Accuracy: 0.1 mm on the tripping points  
 Operating Torque/Force: 53 Inch-Pounds (6Nm)

**Specification:**

Description: XCKN Limit Switch Plastic roller lever plunger horizontal actuation  
 Body Style/Type Description: IEC OsiSense Limit Switches XCKN Light Duty Monolithic 30mm Plastic Body  
 Head Type: Plastic roller lever plunger horizontal actuation  
 Lever Arms:  
 Body with Contact Type: 2-pole N.O./N.C. make before break, slow break  
 Conduit Thread: ISO M20x1  
 Ampere Rating Continuous: 10A  
 Maximum Voltage Rating: 240VAC/250VDC  
 Actuation: Horizontal - One Way  
 Actuator Action: Momentary  
 Lever Arm Length: 20.2mm  
 Roller Dimension: 14 x 5.5mm  
 Roller Material: Thermoplastic  
 Contact Configuration: 1 N.O./1 N.C.  
 Contact Operation: Break before make, slow break  
 Connection Type: Conduit Entrance (ISO M20x1.5)  
 Head Material: Plastic  
 Positive Opening: Yes  
 Cable Length: