


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
XUJK803538



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Diffuse with Background Suppression:
 Diffuse:
 Polarized Retroreflective:
 Thru Beam:
 Retroreflective:
 Circuit Type:
 Output Mode: Light Operate
 Power: DC
 Voltage Range: 24 VDC
 Max Load:
 Max Switching Frequency : 50 Hz
 Temp Range: -25° to 60° C (-13° to 140° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: 67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Proximity Diffuse / 4-20mA & 0-10VDC Output
 Description: Photoelectric, Proximity Diffuse / 4-20mA & 0-10VDC Output, Rectangular, 24 VDC
 Body Style: Rectangular
 Diameter:
 Housing Material: Plastic - PEI
 Face Material:
 Adjustment: No
 Cable Size:
 Connector Type: Cable gland
 Special Features: Load must be: Current < 1K ohm, Voltage >1K ohm