


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XCKN2921P20



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Terminal Type: Screw Clamp
 Enclosure Rating: NEMA 12, 4X Indoor; IP65
 Approvals: UL # E164353 - CSA # 164581 - CE Marked
 Weight: 0.070 kg (0.150 lb)
 Conforming to Standards: CENELEC EN 50047
 RoHS: Yes
 Operating Temperature Range: -13 to 158 ° F
 Shock Resistance: 50G
 Vibration Resistance: 25G
 Max. Actuation Speed : 1 m/s
 Repeat Accuracy: 0.1 mm on the tripping points
 Operating Torque/Force: 53 Inch-Pounds (6Nm)

Specification:

Description: XCKN Limit Switch Plastic roller lever plunger horizontal actuation
 Body Style/Type Description: IEC OsiSense Limit Switches XCKN Light Duty Monolithic 30mm Plastic Body
 Head Type: Plastic roller lever plunger horizontal actuation
 Lever Arms:
 Body with Contact Type: 2-pole N.C./N.C. snap action
 Conduit Thread: ISO M20x1
 Ampere Rating Continuous: 10A
 Maximum Voltage Rating: 240VAC/250VDC
 Actuation: Horizontal - One Way
 Actuator Action: Momentary
 Lever Arm Length: 20.2mm
 Roller Dimension: 14 x 5.5mm
 Roller Material: Thermoplastic
 Contact Configuration: 1 N.C./1 N.C.
 Contact Operation: Snap Action
 Connection Type: Conduit Entrance (ISO M20x1.5)
 Head Material: Plastic
 Positive Opening: Yes
 Cable Length: