

Note:

Drawings Not To Scale
Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Part No.:

XVUC020



Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

UL, CSA, CE, RoHS IP 65

24V AC/DC

Agency Approvals:
Ingress Protection:
Rated Voltage:
Power Consumption:
Sound Level:
Frequency of Buzzer:
Color of Lights:
Light Source:
Frequency of Flashing Lights:
El. Shock Res. EN/IIEC 61140:
Storage Temperature:

Storage Temperature:
Operating Temperature: -40~+70°C -25~+50°C

Description:
Material - Lens Unit:
Material - closure plate:
Material - Body:
Material - Pole:

Material -terminal cover:

Specification:

60mm Tower Body extender, Black, 24V AC/DC

PC(UL94 V-0) PBT + ABS(UL94 V-0)