



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**XX918A1A1L2**



**Telemecanique**  
Sensors

Telemecanique Sensors  
1875 Founders Drive  
Dayton, OH 45420-4017  
Customer Care Center : 1-800-435-2121  
Web : [www.tesensors.com](http://www.tesensors.com)

**Technical Information:**

Sensing Window: 69.9 mm (2.75 in)  
 Far Limit: 101.6 mm (4.0 in)  
 Sensing Range:  
 Circuit Type:  
 Output Mode: Inverse 0 to 10 V  
 Volts Type: DC  
 Voltage Range: 15-24 VDC  
 Max Load: 1k ohm  
 Current Consumption: 50 mA  
 Sonic Frequency: 500 Hz  
 Temp Range: 0° to 60° C (32° to 140° F)  
 NEMA Type: 4X (indoor use only)  
 IP Rating: IP67  
 Standards: UL, CE Rohs

**Specification:**

Sensor Type: Ultrasonic Sensor  
 Description: Ultrasonic Sensor, Analog - Voltage (V), 18 mm Barrel, 15-24 VDC  
 Body Style: Barrel  
 Diameter: mm  
 Housing Material:  
 Face Material: Silicone Rubber  
 Field Configurable: No  
 Functionality:  
 Cable Size: 3.0 m (10 ft)  
 Connector Type:  
 Special Features: