



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XS108BLPAM12



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Detecting Distance: 1.5 mm (0.05 in)
 Circuit Type: PNP
 Output Mode: NO
 Volts Type: DC
 Voltage Range: 12-24 VDC
 Max Load: 50 mA
 Shielding: Shielded
 Max Switching Frequency: 3000 Hz
 Temp Range: -25° to 70° C (-13° to 158° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: IP67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Inductive
 Description: Proximity Sensor, Inductive, 8 mm Barrel, 12-24 VDC, Shielded
 Body Style: Barrel
 Diameter: mm
 Housing Material: Nickel Plated Brass
 Cable Size:
 Connector Type: M12
 Special Features: OEM Focused