



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

XS1N12NA349



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Detecting Distance: 4.0 mm (0.15 in)
 Circuit Type: NPN
 Output Mode: NO
 Volts Type: DC
 Voltage Range: 12-24 VDC
 Max Load: 200 mA
 Shielding: Shielded
 Max Switching Frequency: 2500 Hz
 Temp Range: -25° to 70° C (-13° to 158° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: IP67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Inductive
 Description: Proximity Sensor, Inductive, 12 mm Barrel, 12-24 VDC, Shielded
 Body Style: Barrel
 Diameter: mm
 Housing Material: Nickel Plated Brass
 Cable Size: 2.0 m (6.6 ft)
 Connector Type:
 Special Features: 360° Indicators and Extended Range