


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**XS230AANAM12**



Telemecanique Sensors  
 1875 Founders Drive  
 Dayton, OH 45420-4017  
 Customer Care Center : 1-800-435-2121  
 Web : www.tesensors.com

**Technical Information:**

Detecting Distance: 22.0 mm (0.85 in)  
 Circuit Type: NPN  
 Output Mode: NO  
 Volts Type: DC  
 Voltage Range: 12-24 VDC  
 Max Load: 200 mA  
 Shielding: Non shielded  
 Max Switching Frequency: 500 Hz  
 Temp Range: -25° to 85° C (-13° to 185° F)  
 NEMA Type: 4X (indoor use only)  
 IP Rating: IP67, IP69K  
 Standards: UL, CE Rohs

**Specification:**

Sensor Type: Inductive  
 Description: Proximity Sensor, Inductive, 30 mm Barrel, 12-24 VDC, Non Shielded  
 Body Style: Barrel  
 Diameter: mm  
 Housing Material: Plastic  
 Cable Size:  
 Connector Type: M12  
 Special Features: