


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

XT130B1NAL2



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Max Range Adj:	10.0 mm (0.394 in)
Circuit Type:	Normally Open
Output Mode:	NPN
Volts Type:	DC
Voltage Range:	12-30 VDC
Max Load :	200 mA
Shielded:	Shielded
Operating Frequency:	150 Hz
Temp Range:	-25° to 70° C (-13° to 158° F)
NEMA Type:	4X (indoor use only)
Standards:	UL, CE Rohs

Specification:

Sensor Type:	Capacitive Sensor
Description:	Proximity Sensor, Capacitive, 30 mm Barrel, 12-30 VDC, Shielded
Body Style:	Barrel
Diameter:	mm
Face Material:	PBT Plastic
Housing Material:	Nickel Plated Brass
Cable Length:	2.0 m (6.6 ft)
Connector Type:	
Special Features:	NO output