


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XUJB06031H60



Telemecanique Sensors
 1875 Founders Drive
 Dayton, OH 45420-4017
 Customer Care Center : 1-800-435-2121
 Web : www.tesensors.com

Technical Information:

Diffuse with Background Suppression:

Diffuse:
 Polarized Retroreflective:
 Thru Beam:
 Retroreflective: 6000.0 mm (236.2 in)
 Circuit Type:
 Output Mode: Dark Operate
 Power: AC/DC
 Voltage Range: 24-240AC / 24-48DC
 Max Load: 2000 mA
 Max Switching Frequency : 20 Hz
 Temp Range: -25° to 55° C (-13° to 131° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: 40
 Standards: UL, CE Rohs

Specification:

Sensor Type: Retroreflective - Kit
 Description: Photoelectric, Retroreflective - Kit, Rectangular, 24-240AC / 24-48DC
 Body Style: Rectangular
 Diameter:
 Housing Material: Plastic - PEI
 Face Material: PMMA
 Adjustment: Pot
 Cable Size:
 Connector Type: Cable gland
 Special Features: 0.3 to 3 second timer; includes bracket and reflector