



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**XX230A32PA00M12**



**Telemecanique**  
Sensors

Telemecanique Sensors  
1875 Founders Drive  
Dayton, OH 45420-4017  
Customer Care Center : 1-800-435-2121  
Web : www.tesensors.com

**Technical Information:**

Sensing Window:  
Far Limit:  
Sensing Range: 203.0 mm to 8.0 m (8.0 in to 26.0 ft)  
Circuit Type: Normally Open  
Output Mode: PNP  
Volts Type: DC  
Voltage Range: 12-24 VDC  
Max Load: 100 mA  
Current Consumption: 100 mA  
Sonic Frequency: 75 Hz  
Temp Range: -20° to 60° C (-4° to 140° F)  
NEMA Type: 4X (indoor use only)  
IP Rating: IP67  
Standards: UL, CE Rohs

**Specification:**

Sensor Type: Ultrasonic Sensor  
Description: Ultrasonic Sensor, Dual-Level - Dual Setpoint, 30 mm Barrel, 12-24 VDC  
Body Style: Barrel  
Diameter: mm  
Housing Material: Glass Epoxy  
Face Material: No  
Field Configurable: No  
Functionality: Default Window: ± 64 mm (2.5 in)  
Cable Size: M12  
Connector Type: M12  
Special Features: