



TERMINAL LUGS DATA

| AMPERES | MAX WIRE      | MIN WIRE     | TYPE  |
|---------|---------------|--------------|-------|
| 600     | (2) 500 KCMIL | (1) #3/0 AWG | AL/CU |

DUAL DIMENSIONS: INCHES  
MILLIMETERS

NOTES:  
 FINISH – TYPE 12 GRAY BAKED ENAMEL  
 TYPE 4, 4X, 5 TYPE 304 STAINLESS STEEL  
 CSA CERTIFIED – FILE #97407  
 ALL NEUTRALS – INSULATED GROUNDABLE  
 FUSIBLE SWITCHES ARE SUITABLE FOR USE AS SERVICE EQUIPMENT  
 SHORT CIRCUIT CURRENT RATINGS:  
 10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES.  
 200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R FUSES HAVING  
 CLASS REJECTIONS KITS INSTALLED OR CLASS J FUSES.

| CATALOG NUMBER |                             | VOLTAGE RATINGS | WIRING DIAG | HORSEPOWER RATINGS |     |        |     |        |     |
|----------------|-----------------------------|-----------------|-------------|--------------------|-----|--------|-----|--------|-----|
| TYPE 12        | TYPE 4,4X,5 STAINLESS STEEL |                 |             | 240VAC             |     | 480VAC |     | 600VAC |     |
|                |                             |                 |             | STD                | MAX | STD    | MAX | STD    | MAX |
| CH326NAWK      | CH326NDS                    | 240VAC          | B           | 75                 | 200 | –      | –   | –      | –   |
| CH366AWK       | CH366DS                     | 600VAC;600VDC   | A           | –                  | –   | 150    | 400 | 200    | 500 |
| CH366NAWK      | CH366NDS                    | 600VAC          | B           | –                  | –   | 150    | 400 | 200    | 500 |
| CHU366AWK      | CHU366DS                    | 600VAC;600VDC   | C           | –                  | 200 | –      | 400 | –      | 500 |

|  |  |
|--|--|
| HEAVY DUTY SAFETY SWITCHES<br>VISIBLE BLADE TYPE<br>600 AMPERE<br>ENCLOSURE – TYPE 12<br>TYPE 4, 4X, 5 STAINLESS STEEL | <br><b>SQUARE D</b><br>by Schneider Electric |
| DWG# 1932C<br>NO.  |  |