



TERMINAL LUGS			
AMPERES	MAX WIRE	MIN WIRE	TYPE
30	#2	#14	AL
60	#2	#14	AL

KNOCKOUTS				
SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	44
E	1.50	38	2.00	51
F	2.00	51	2.50	64

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATING	AMPERE RATING	WIRING DIAG	120 VAC		240 VAC				CORNER ③ GROUNDED DELTA SYSTEM		480 VAC				CORNER ③ GROUNDED DELTA SYSTEM		600 VAC				125 VDC ②		250 VDC ②		600 VDC ②			
				1PH ①		1PH ①		3PH		STD	MAX	STD	MAX	1PH ①		3PH		STD	MAX	1PH ①		3PH		STD	MAX	STD	MAX	STD	MAX
				STD	MAX	STD	MAX	STD	MAX					STD	MAX	STD	MAX			STD	MAX	STD	MAX						
DT321RB	240VAC:250VDC	30	A	0.5	2	1.5	3	3	7.5	3	7.5	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	2	3	5	5	NA	NA	
DT361RB	600VAC:600VDC	30	A	0.5	2	1.5	3	3	7.5	3	7.5	3	7.5	5	15	5	15	3	10	7.5	20	2	3	5	5	10	15		
DT322RB	240VAC:250VDC	60	A	1.5	3	3	10	7.5	15	7.5	15	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	NA	5	10	10	NA	NA		
DT362RB	600VAC:600VDC	60	A	1.5	3	3	10	7.5	15	7.5	15	5	20	15	30	15	30	10	25	15	50	NA	5	10	10	25	30		

NOTES:
 UL LISTED - FILE E-2875
 FINISH - GRAY BAKED ENAMEL
 SHORT CIRCUIT CURRENT RATING:
 10,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS H OR K FUSES.
 200,000 AMPERES WHEN USED IN CONJUNCTION WITH CLASS J OR R FUSES.
 ① FOR SINGLE PHASE HP RATINGS USE 2 SWITCHING POLES.
 ② FOR DC RATINGS USE 2 SWITCHING POLES.
 ③ FOR CORNER GROUNDED DELTA SYSTEM, USE 2 SWITCHING POLES AND INSTALL NEUTRAL FOR GROUNDED CONDUCTOR.

HEAVY DUTY SAFETY SWITCHES
 VISIBLE BLADES
 30-60 AMPERE
 ENCLOSURE - TYPE 3R
 FUSIBLE

DWG# 3200
NO.