



J:\wip\209\control online\5868.DWG 07/22/2008 12:15:15 PM

CATALOG NUMBER	PRIMARY VOLTAGE	SECONDARY VOLTAGE	50/60 Hz 1 PHASE		APPROXIMATE WEIGHT (Lbs/Kg)
			UL/cUL/CSA/NOM RATINGS (VA)	CE RATINGS (VA)	
9070T1000D1	220/440 230/460 240/480	110 115 120	1000	630	20.6 / 9.3
9070T1000D3	208	120	1000	630	20.3 / 9.2
9070T1000D4	277	120	1000	630	20.9 / 9.4
9070T1000D5	550 575 600	110 115 120	1000	630	20.6 / 9.3
9070T1000D12	440 460 480	220 230 240	1000	630	20.2 / 9.1
9070T1000D14	208	24	1000	N/A	20.3 / 9.2
9070T1000D15	240/480	24/120	1000	630	20.7 / 9.3
9070T1000D22	480	277	1000	630	20.3 / 9.2
9070T1000D24	110 115 120	110 115 120	1000	630	20.2 / 9.1
9070T1000D31	220/440 230/460 240/480	110/220 115/230 120/240	1000	630	20.4 / 9.2
9070T1000D33	380/400/415	115/230	1000	630	20.8 / 9.4
9070T1000D37	550 575 600	110/220 115/230 120/240	1000	630	20.8 / 9.4
9070T1000D55	110/220 115/230 120/240	110/220 115/230 120/240	1000	630	20.9 / 9.4
9070T1000D60	277	120/240	1000	630	20.8 / 9.4
9070T1000D62	600	240	1000	630	20.3 / 9.2



FILES/STANDARDS:  
 UL/cUL FILE: E61239  
 CSA FILE: LR37055  
 CE: TUV CERTIFIED TO 61558  
 NOM 117

1000VA—CONTROL POWER TRANSFORMER  
 9070 TYPE T  
 CATALOG NUMBERS: FROM CHART



DWG# 5868  
 NO.