



**NOTES:**

1. MUST BE 4 WIRE + GROUND PROVIDED WYE-SOURCE.
- △ 2. SINGLE MAINS INSTALLATION IS A DEFAULT.  
DUAL MAINS OPTION REQUIRES CUSTOM ENGINEERING. PLEASE REFER TO APC CUSTOM ENGINEERING GROUP AND DRAWING# CEG-SUVT10K30F2-WD FOR DETAILS
3. CABLING PROVIDED BY OTHERS.
4. ALL AC POWER CABLING IS 4 WIRE + GROUND AT 208VAC 3-PHASE.
5. POWER WIRING AND CONTROL WIRING MUST BE IN SEPARATE CONDUITS
- △ 6. THESE CONNECTIONS ARE APPLICABLE TO APC XR ENCLOSURE ONLY
7. INSTALLATION MUST COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL CODES

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.		TITLE: SMART-UPS VT 10-30kVA 208V 3PH SINGLE MAINS MBP WITHOUT DISTRIBUTION PANEL SYSTEM WIRING DIAGRAM		DWG NO: SUVTMBP10K30F1-WD		REV. 1	
PROJECT: SUBMITTAL DRAWINGS		SHEET 1 OF 1		DRAWN BY: E.DICHENKO		08/17/05	
				CHECKED BY: J.RING / F.DIOSA		08/17/05	
				ENGINEER: R.HANSEN / E.SILVA		08/17/05	

