

# 5505

## SCADAPack RTD Input Module



### At a glance

- Input values scaled and linearized
- Data returned as 32-bit floating point number
- Low power consumption
- Automatic 3-wire RTD compensation
- 5503 emulation mode for legacy systems

The SCADAPack™ 5505 RTD input module is part of the SCADAPack family of I/O Expansion and Communication modules, providing flexible I/O and telemetry options.

With the addition of I/O Expansion modules, any<sup>1</sup> SCADAPack Smart RTU is easily expandable from its base I/O configuration to more than 700 process I/O points. Available for a wide range of process I/O requirements, from digital and analog I/O to I/O simulators and a UPS module, a maximum of twenty I/O modules may be connected for an expansion of up to 512 digital outputs, 512 digital inputs, 128 analog inputs, 64 counters and 64 analog outputs, on some models.

# 5505

## SCADAPack RTD Input Module

### Specifications – 5505 RTD input module

#### General

Input Points	4, RTD
RTD Type	100 $\Omega$ platinum, 3 and 4-wire, auto-detection and compensation
Calibration	0.00385 $\Omega$ / $^{\circ}\text{C}$ standard based on ASTM E 1137/E 1137M-04, ITS-90
Ranges	<p>5505: Can be configured to return data in <math>\Omega</math>, <math>^{\circ}\text{C}</math>, <math>^{\circ}\text{F}</math> or <math>^{\circ}\text{K}</math></p> <ul style="list-style-type: none"> <li>-200...800 <math>^{\circ}\text{C}</math> (-328...1472 <math>^{\circ}\text{F}</math>)</li> <li>0 to 500 <math>\Omega</math></li> </ul> <p>5503 Emulation: Dipswitch selectable</p> <ul style="list-style-type: none"> <li>0...200 <math>^{\circ}\text{C}</math> (32...392 <math>^{\circ}\text{F}</math>)</li> <li>-100...100 <math>^{\circ}\text{C}</math> (-148...212 <math>^{\circ}\text{F}</math>)</li> <li>-200...0 <math>^{\circ}\text{C}</math> (-328...32 <math>^{\circ}\text{F}</math>)</li> <li>0...800 <math>^{\circ}\text{C}</math> (32...1472 <math>^{\circ}\text{F}</math>)</li> <li>0...400 <math>^{\circ}\text{C}</math> (32...752 <math>^{\circ}\text{F}</math>)</li> <li>0 to 400 <math>\Omega</math></li> </ul>
Data Format	<ul style="list-style-type: none"> <li>5505: 32-bit floating point and 12 status bits</li> <li>5503 Emulation: 16-bit signed integer</li> </ul>
Resolution	<ul style="list-style-type: none"> <li>5505: &gt; 17-bit effective</li> <li>5503 Emulation: 15-bit</li> </ul>
RTD Status	<ul style="list-style-type: none"> <li>RTD is good (not open)</li> <li>RTD in range</li> <li>RTD 3 or 4-wire</li> <li>RTD status not available in 5503 Emulation</li> </ul>
Accuracy on RTD Ranges	Percent of full scale over operational temperature range including linearization errors: +0.10%/-0.05%
Accuracy on 0...500 $\Omega$	Percent of full scale over operational temperature range: $\pm 0.03\%$
Excitation Current	4 mA, 7.2% duty cycle in 4-wire mode, 14.4% in 3-wire mode, 250 ms scan interval
Line Resistance	100 $\Omega$ max., in each line
Converter Type	24-bit delta-sigma
Response Time	380 ms typical for 10% to 90% signal change at minimum filter setting
Transient Protection	2.5 kV surge-withstand capability as per ANSI/IEEE C37.90.1-1989
Isolation	Isolation from logic supply and chassis, voltage 500 Vrms
5 Vdc Power Requirements	6 mA
11 - 30 Vdc Power Requirements	<p>12 Vdc operation: 4 mA</p> <ul style="list-style-type: none"> <li>plus 0.6 mA per 4-wire RTD</li> <li>plus 1.2 mA per 3-wire RTD</li> </ul> <p>24 Vdc operation: 2.2 mA</p> <ul style="list-style-type: none"> <li>plus 0.3 mA per 4-wire RTD</li> <li>plus 0.6 mA per 3-wire RTD</li> </ul>

# 5505

## SCADAPack RTD Input Module

### Specifications – 5505 RTD input module continued

#### General

11...30 Vdc - Connector	Removable. Shared with RTD inputs 0-1
11...30 Vdc - Isolation	Isolation from logic supply and chassis
Terminations	8 and 10-pole, removable terminal block, 12...22 AWG, 15 A contacts
Dimensions	74 mm wide x 124 mm high x 45 mm deep (2.90 in. x 4.90 in. x 1.80 in.)
Mounting	7.5 x 35 DIN rail
Packaging	Corrosion resistant zinc plated steel with black enamel paint
Environment	5% RH to 95% RH, non-condensing, -40...70 °C (-40...158 °F) operation, -40...85 °C (-40...185 °F) storage
Safety	<ul style="list-style-type: none"> <li>• Non-Incendive Electrical Equipment for Use in Class I, Division 2</li> <li>• Groups A, B C and D Hazardous Locations</li> <li>• ATEX II 3G and IECEx: Ex nA IIC T4 per EN 60079-15, protection type n (Zone 2)</li> </ul>

### Model Code – 5505 RTD input module

Part number	Model	Description
TBUX297318	5505	RTD input module

**Note:** This product is RoHS-compliant. Accessories sold separately.

**Footnote: 1.** Some I/O Expansion modules are specific to SCADAPack 300 RTUs, others are specific to SCADAPack E RTUs. The SCADAPack 100 does not support any such module.

**Disclaimer:** Schneider Electric reserves the right to change product specifications. For more information visit [www.se.com](http://www.se.com).

#### Schneider Electric Systems USA

Process Automation SCADA & Telemetry  
38 Neponset Avenue, Foxboro, Massachusetts 02035 USA Direct  
Worldwide: +1 (613) 591-1943  
Email: [telemetrysolutions@se.com](mailto:telemetrysolutions@se.com)  
Toll Free within North America: +1 (888) 267-2232  
[www.se.com](http://www.se.com)

Life Is On 

Part Number TBULM08001-73 v08

© 2019 Schneider Electric. All Rights Reserved. Schneider Electric, Life Is On Schneider Electric, and SCADAPack are trademarks and the property of Schneider Electric SE, its subsidiaries and affiliated companies. All other trademarks are the property of their respective owners. February 2021