



NOTES:

1. PLEASE REFER TO APC INSTALLATION GUIDE
2. Q1 TO Q6 WITH 2NO/2NC AUXILIARY CONTACTS.
3. Q7, Q8 DC RATED THERMAL MAGNETIC TRIP MOLDED CASE CIRCUIT BREAKER WITH 24VOLT DC UNDERVOLTAGE RELEASE (UVR) AND 2NO/2NC AUXILIARY CONTACTS.
4. PLEASE REFER TO THE INSTALLATION MANUAL FOR THE BREAKER SETTINGS OF Q1, Q3, Q4 & Q5.

△ 5. UPS AND STATIC BYPASS WITHSTAND RATING (Icw)= 200kA

△ 6. SEE BATTERY INSTALLATION INFORMATION

7. ALL AC POWER CABLING IS L1,L2,L3,N,PE.

8. UPS INPUT AND OUTPUT CONDUCTORS MUST BE IN SEPARATE CABLE RUNS.

9. DC CABLING SHOULD BE SEGREGATED FROM AC CABLING

10. POWER WIRING AND CONTROL WIRING SHOULD BE SEGREGATED.

11. - - - - - = CABLING PROVIDED BY OTHERS

12. INSTALLATION MUST COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL CODES.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE: SYMMETRA MW UPS
380/400/415V AC, 3PH, 1x1400kW
DUAL MAINS
SYSTEM ONE LINE DIAGRAM
PROJECT: SUBMITTAL DRAWING SHEET 1 OF 1

DWG NO: SYMF1400K1400H2C1-SD
DRAWN: BALAMURUGAN 15/03/07
CHECKED: S WAGH 15/03/07
ENGINEER: S WAGH 15/03/07

REV. 1
PROJECTION

