


NEMA TYPE 1



TERMINAL LUGS †			
AMPERES	CONDUIT SIZE	DIAMETER	
60	#3 AWG	#14 AWG	CU OR AL

SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1.00	25	1.38	35
D	1.25	32	1.75	44

DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEAN PHOSPHATIZED STEEL.
 UL LISTED - FINE E-2875.
 ALL NEUTRALS - INSULATED GROUNDABLE.
 SUITABLE FOR USE AS SERVICE EQUIPMENT.
 SHORT CIRCUIT RATINGS:
 10,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS H OR K FUSES
 100,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS R FUSES
 WHEN MOUNTING THESE SWITCHES, ALLOW 3.00/[76] MINIMUM CLEARANCE BETWEEN ENCLOSURES FOR OPENING OF SIDE HINGED DOOR.
 ▲USE OUTER SWITCHING POLES.
 ●FOR CORNER GROUNDED DELTA SYSTEMS ONLY.
 †LUGS SUITABLE FOR 60°C OR 75°C CONDUCTORS.

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG	AMPERE RATING	HORSEPOWER RATINGS			
				240VAC			
				STD		MAX	
		1Ø	3Ø	1Ø	3Ø		
D222N	240VAC	A	60	3 ▲	7.50 ●	10	15 ●
D322N	240VAC	B	60	3	7.50	10	15

GENERAL DUTY SAFETY SWITCHES
 VISIBLE BLADE TYPE
 60 AMPERE
 ENCLOSURE - NEMA TYPE 1 GENERAL PURPOSE

SQUARE D
 by Schneider Electric

DWG# 1859
 NO.