

CLASS 10 OVERLOAD RELAYS



CURRENT SETTING RANGE (AMPS)	CATALOG NUMBER
23-32	LR2 D33 53
30-40	LR2 D33 55
37-50	LR2 D33 57
48-65	LR2 D33 59
55-70	LR2 D33 61
63-80	LR2 D33 63

CLASS 20 OVERLOAD RELAYS

CURRENT SETTING RANGE (AMPS)	CATALOG NUMBER
17-25	LR2 D35 22
23-32	LR2 D35 53
30-40	LR2 D35 55
37-50	LR2 D35 57
48-65	LR2 D35 59
55-70	LR2 D35 61
63-80	LR2 D35 63

(1) = SELECT DESIRED SUFFIX FOR COMPLETE CATALOG NUMBER

Electrical Clearance/Wire Bending Space



Catalog Number: LR2 D3(1) on LC1 D65
 Ratings: Ratings shown are for LR2 D3(1) only. For contactor ratings see contactor file.
 UL File/CCN: E39281/NKCR
 CSA File/Class: LR43364/3211 03
 Meets Standards: IEC 947
 Weight: .51kg
 Wire Size: Power #4-#6 / Control #10-#18
 Terminal torque: 75 LB-IN
 Mounting Hwd: 35mm DIN rail, #8 screws

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

DO NOT SCALE DRAWING
 UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION
 TOLERANCES
 UNLESS OTHERWISE SPECIFIED
 2 PLACE DECIMALS ± .01

IEC STARTER
 LC1 D65 WITH LR2 D3(1) OVERLOAD

 **SQUARE D COMPANY**

DWG# E0201901-01
 No.