

CLASS 10 OVERLOAD RELAYS


CURRENT SETTING RANGE (AMPS)	CATALOG NUMBER
23-32	LR2 D33 53
30-40	LR2 D33 55
37-50	LR2 D33 57
48-65	LR2 D33 59
55-70	LR2 D33 61
63-80	LR2 D33 63

CLASS 20 OVERLOAD RELAYS


CURRENT SETTING RANGE (AMPS)	CATALOG NUMBER
17-25	LR2 D35 22
23-32	LR2 D35 53
30-40	LR2 D35 55
37-50	LR2 D35 57
48-65	LR2 D35 59
55-70	LR2 D35 61
63-80	LR2 D35 63

(1) = SELECT DESIRED SUFFIX FOR COMPLETE CATALOG NUMBER

Electrical Clearance/Wire Bending Space



Minimum to wall or barrier to insure adequate wire bending space to lug surface when the maximum wire size is used. REF. NEC 430-10



Catalog Number: LR2 D3(1) on LC1 D80
 Ratings: Ratings shown are for LR2 D3(1) only. For contactor ratings see contactor file.
 UL File/CCN: E39281/NKCR
 CSA File/Class: LR43364/3211 03
 Meets Standards: IEC 947
 Weight: .51kg
 Wire Size: Power #4-#6 / Control #10-#18
 Terminal torque: 75 LB-IN
 Mounting Hwd: 35mm DIN rail, #10 screws

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

DO NOT SCALE DRAWING
 UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION
TOLERANCES
 UNLESS OTHERWISE SPECIFIED
 2 PLACE DECIMALS ± .01

IEC STARTER
 LC1 D80 WITH LR2 D3(1) OVERLOAD

SQUARE D COMPANY

DWG# E0202001-01
 NO.