


KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO124L150G	120/240VAC 1Ø 3W	150	24	24	#4-250
QO124M150		150	24	24	
QO124M200		200	24	24	
QO13040L200G		200	30	40	
QO13040L200GC		200	30	40	
QO13040M200		200	30	40	
QO13040M200C		200	30	40	
QO130L150G		150	30	30	#4-250
QO130L150TC		150	30	30	
QO130L200G		200	30	30	
QO130M150		150	30	30	
QO130M150C		150	30	30	
QO130M200		200	30	30	
QO130M200C		200	30	30	

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED, GROUNDABLE.
LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
LOAD CENTERS WITH "T" IN CATALOG NUMBER INCLUDE A FACTORY INSTALLED EQUIPMENT GROUND BAR KIT.

QO LOAD CENTERS
GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE
INDOOR



DWG# 3006
NO.