



TYPE CODE (1)	MAXIMUM CURRENT	MAXIMUM VOLTAGE
D1	0.1 AMPS	250VAC/65VDC
D5	0.5 AMPS	
D8	0.8 AMPS	
10	1.0 AMPS	
12	1.2 AMPS	
15	1.5 AMPS	
20	2.0 AMPS	
25	2.5 AMPS	
30	3.0 AMPS	
40	4.0 AMPS	
50	5.0 AMPS	125VAC/65VDC
70	7.0 AMPS	
100	10.0 AMPS	
150	15.0 AMPS	

THESE MAXIMUM CURRENT VALUES ASSUME THE USE OF INSULATED COPPER CONDUCTORS WITH 75° C TEMPERATURE RATING, AND ARE CALCULATED BASED ON NEC ARTICLE 310, TABLE 310-16.



FRONT



RIGHT

Catalog Number: 9080-GCB(1)  
 Ratings: SEE CHART  
 UL File/CCN: E152B41/QVNU2  
 CSA File/Class: LR25490/184-N-90  
 Meets Standards: -  
 Weight: 0.18 lbs.  
 Wire Size: #16-#10 AWG  
 Terminal Torque: 8-10 lb./in.  
 Mounting Hwd.: TERMINAL MOUNTING CHANNEL 35mm DIN RAIL

DUAL DIMENSIONS: INCHES MILLIMETERS

TERMINAL BLOCKS  
 (TYPE G) (CONTROL CIRCUIT PROTECTION)  
 CLASS 9080 TYPE GCB(1)



DWG# E0801701-01  
 NO.