





NOTES:

1. MUST BE 4 WIRE + GROUND PROVIDED WYE-SOURCE.
- △ 2. FOR DUAL MAINS INSTALLATION 3 BRIDGE BUS BARS MUST BE REMOVED. BYPASS INPUT CAN BE PROVIDED VIA UTILITY SOURCE OR OTHER NON-SYNCHRONIZED SOURCE. PLEASE CONTACT APC IF DUAL SOURCES ARE BOTH SEPARATELY DERIVED POWER SYSTEMS
3. CABLING PROVIDED BY OTHERS.
4. ALL AC POWER CABLING IS 4 WIRE + GROUND AT 208VAC 3-PHASE.
5. POWER WIRING AND CONTROL WIRING MUST BE IN SEPARATE CONDUITS
- △ 6. THESE CONNECTIONS ARE APPLICABLE TO APC XR ENCLOSURE ONLY
7. OUTPUT OVERCURRENT PROTECTION MUST BE PROVIDED BY OTHERS RECOMMENDED OUTPUT BREAKER RATING
FOR 10kVA IS 35A, 15kVA IS 60A, 20kVA IS 70A AND FOR 30kVA IS 110A.
8. INSTALLATION MUST COMPLY WITH ALL APPLICABLE NATIONAL AND LOCAL CODES

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE: SMART-UPS VT
10-30kVA 208V 3PH DUAL MAINS
SYSTEM WIRING DIAGRAM

PROJECT: SUBMITTAL DRAWINGS SHEET 2 OF 2

DWG NO:	SUVT10K30F2-WD	REV:	1
DRAWN BY:	C KRISHNA	CHECKED BY:	J.RING / F.DIOSA
		ENGINEER:	R.HANSEN / E.SILVA
			08/17/05

APC[®]
AMERICAN POWER CONVERSION
132 FAIRGROUNDS RD
WEST KINGSTON, RI 02892