



**NOTES:**

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
- △ 2. SHALL BE L1, L2, L3, N, PE (PROVIDED BY OTHERS).
- △ 3. ----- = AC/DC CABLING (PROVIDED BY OTHERS).
4. PLEASE REFER TO APC INSTALLATION GUIDE.
- △ 5. DC CABLING SHOULD BE SEGREGATED FROM AC CABLING.
6. ALL AC POWER CABLING IS L1, L2, L3, N, PE.
7. UPS INPUT AND OUTPUT CABLES SHOULD BE SEGREGATED.
- △ 8. FOR DUAL MAINS INSTALLATION 3 BRIDGE BUS BARS BETWEEN MAIN AND BYPASS INPUTS SHALL BE REMOVED.
- △ 9. BYPASS INPUT CAN BE PROVIDED VIA MAINS INPUT OR OTHER NON-SYNCRONIZED SOURCE. PLEASE CONTACT APC IF DUAL SOURCES ARE BOTH SEPARATELY DERIVED POWER SYSTEMS.
10. POWER WIRING AND CONTROL WIRING SHOULD BE SEGREGATED.
11. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION.
12. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.
13. OUTPUT OVERCURRENT PROTECTION SHALL BE PROVIDED BY OTHERS. RECOMMENDED OUTPUT BREAKER RATING 25A.



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: SMART-UPS VT 15kVA WITHOUT INTERNAL BATTERY INPUT: 3x400/230V DUAL MAINS OUTPUT: 3x400/230V 10kVA SYSTEM ONE LINE  
PROJECT: STD SUBMITTAL DRAWINGS SHEET 1 OF 1

DWG NO:	SUVTP15KH2SNB-SD	REV.	1
DRAWN BY:	V BUSH	15-APR-11	PROJ
ENGINEER:	B H NIELSEN	15-APR-11	ANGLE
APPROVED BY:	C LARSEN	15-APR-11	N.A.