

1	2		3	4	5	6	7	8	9	10	
<p>A</p> <p>This technical information, contained in this document is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in their position. Drawn out with operating mechanism discharged and all power sources off.</p>	Folio	Designation	Indice de modification			Folio	Designation	Indice de modification			
	Sheet	Designation	Revision			Sheet	Designation	Revision			
	001	FRONT PAGE	00								
	002	SUMMARY	00								
	003	FUNCTIONAL PLATE	00								
	004	LAYOUT	00								
	005	WIRE LIST	00								
006	PART LIST	00									
<p>B</p>											
<p>C</p> <p>Les informations techniques contenues dans ce document (y compris les appareils, équipements, Schneider Electric Industries S.A.S. et ne peuvent être utilisés ou divulgués à des tiers sans le consentement écrit de Schneider Electric Industries S.A.S. Les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - "disarmés" - débranchés - toutes sources coupées.</p>											
<p>D</p>											

Archivage
Microfilm

SUMMARY

CELLEAN OFFER




OGH9353603

Project - No commande
Project - Order No.


Indice
Rev
00

Folio
Sheet
002


Nota: For the advanced control see the Tesys catalogue and choose the advanced option, see sheet A4/12



AUXILIARY SIGNALING CONTACTS MODULE (OPTION)



AUXILIARY SIGNALING CONTACTS BLOCK (OPTION)



TO MOTOR

This technical information is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those diagrams and diagrams permitted after order booking are binding for execution. All devices shown in this diagram are in open position. Drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document (sauf la propriété intellectuelle de Schneider Electric Industries S.A.S.) ne peuvent être utilisées ou divulguées à des tiers ou à des tiers tiers sans son accord écrit. Seuls nos engagements pour l'exécution des plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - débranchés - toutes sources coupées.

FUNCTIONAL PLATE
DOLD15
TESYS U
WIRED VERSION
1 WAY ROTATION

CELLEAN OFFER



QGH9353603
 Projet - No commande
 Project - Order No. Indice Rev 00
 Folio Sheet 003

A

B

C

D

A


B

C

D


This technical information is provided in this document as the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism discharged and all power sources off.

Les informations techniques contenues dans ce document sont la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans son accord écrit. Seuls ceux autorisés par le service client sont contraignants. Les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouverte - débranchés - toutes sources coupées.



DO NOT DISCONNECT THE GROUND WIRE BEFORE DISCONNECTING THE MOTOR CABLE

APPROXIMATE WEIGHT : 1500 g



Ind.	Date	Modification	Archiv.	Ind.	Date	Modification	Archiv.
00	10/01/2017	Edition originale					

LAYOUT
DOLD15
TESYS U
WIRED VERSION
1 WAY ROTATION

CELLEAN OFFER



QGH9353603		Indice Rev	Folio Sheet
Projet - No commande Project - Order No.		00	004

1	2		3		4	5	6	7	8	9	10
Type of circuit	Electrical Features		Wire Destination		Sheet N°	Designation	Color	Section	Wire Type	Câble end	
	P(kW)	I(A)	From	To						From	To
POWER CIRCUIT	15 kW	32 A	XP1.1	QM1.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	6 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED
			XP1.2	QM1.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	6 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED
			XP1.3	QM1.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	6 mm²	H07V-K	CABLE END INSULATED LONG SIZE	CABLE END INSULATED
CONTROL CIRCUIT			XAUX1.1	QM1.A1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.2	QM1.A2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.5	QM1.21	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.4	QM1.13	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.3	QM1.14	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			QM1.14	QM1.22	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.8	QM1.17	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.7	QM1.97	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			XAUX1.6	QM1.98	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED
			QM1.98	QM1.18	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED	CABLE END INSULATED

This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position, drawn out with operating mechanism disassembled and all power sources off.

Les informations techniques contenues dans ce document (sauf la propriété exclusive de Schneider Electric Industries S.A.S. et ne peuvent être utilisées ou divulguées à des tiers) ou les droits ou les savoirs sans son accord écrit. Seuls nos engagements sur exécution, les plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - débranchés - toutes sources coupées.

WIRE LIST
 DOLD15
 TESYS U
 WIRED VERSION
 1 WAY ROTATION

CELLEAN OFFER



QGH9353603
 Projet - No commande
 Project - Order No.

Indice Rev	Folio Sheet
00	005

A

B

C

D

A

B

C

D

This technical information contained in this document is the exclusive property of Schneider Electric Industries S.A.S. and cannot be used or disclosed to third parties of any kind without its written consent. Only those drawings and diagrams permitted after order booking are binding for execution. All devices shown in this diagrams are in open position. Drawn out with operating mechanism disengaged and all power sources off.

Les informations techniques contenues dans ce document (sauf le matériel exclu) sont la propriété exclusive de Schneider Electric S.A.S. et ne peuvent être utilisées ou divulguées à des tiers sans son accord écrit. Seuls nos engagements pour l'exécution des plans et schémas remis après enregistrement de la commande. Les appareils représentés sur ce schéma sont en position ouvert - débranchés - toutes sources coupées.

TAG	SHEET	DESCRIPTION	MANUFACTURER	MANUFACTURER REF.	QTY
QM1	003	COIL TERMINALS	SCHNEIDER ELECTRIC	LU9BN11	1
QM1	003	BLANK'G COVER LOC AUX CON'T/F	SCHNEIDER ELECTRIC	LU9C1	1
QM1	003	FAULT+READY AUX CONTACT	SCHNEIDER ELECTRIC	LUA1C20	1
QM1	003	SCREW CLAMP BASE 32A	SCHNEIDER ELECTRIC	LUB320	1
QM1	003	UNIT 8-32A 24VDC	SCHNEIDER ELECTRIC	LUCM32BL	1
XAUX1	003	MOVING CONNECTOR SINGLE 8P 12A	SCHNEIDER ELECTRIC	LGYDC8APM	1
XP1	003	MOVING CONNECTOR 3P 32A	SCHNEIDER ELECTRIC	LGYDC3P32M2S	1
		FUNCTION PLATE H300 x W100 2 WINDOWS VERSION A	SCHNEIDER ELECTRIC	NSYME03012A	1
		DIN RAIL, WIDTH: 35mm, HEIGHT: 15mm, LENGTH: 100mm	-----	DIN RAIL T1	1

00	10/01/2017	Edition originale / First issue							
Ind. Rev	Date	Modification /	Modification	Archiv. Micro-filmed	Ind. Rev	Date	Modification /	Modification	Archiv. Micro-filmed

PART LIST
DOLD15
TESYS U
WIRED VERSION
1 WAY ROTATION

CELLEAN OFFER



QGH9353603
Project - No commande
Project - Order No.

Indice Rev	Folio Sheet
00	006