




END WALL
CONDUIT ENTRANCE
TOP & BOTTOM



BOX WITH INTERIOR

BOX SIDE

TYPICAL FRONT

DUAL DIMENSIONS: INCHES
MILLIMETERS

PRI V TO SEC V	208 TO 120	240 TO 120	277 TO 120	480 TO 120
INTERIOR CATALOG NO. (1)	SIP07BA	SIP07CA	SIP07DA	SIP07EA
INTERIOR DESCRIPTION	7.5 kVA ISOLATION POWER PANEL, NQ INTERIOR CONTAINING EIGHT 20A 2-POLE PLUG-ON BREAKERS, SPACE FOR EIGHT 2-POLE (20A MAX), IG6 LINE ISOLATION MONITOR, GROUND BAR WITH 20 TERMINALS			
CB MAIN	QO 45A 2-POLE	QO 40A 2-POLE	HG 35A 2-POLE	HG 20A 2-POLE
TRANSFORMER CATALOG NO. (1)	SXM07BA	SXM07CA	SXM07DA	SXM07EA
TRANSFORMER DESCRIPTION	7.5 kVA, SINGLE PHASE, 115°C RISE, 180 C INSULATION, ELECTROSTATIC SHIELD, 40dB SOUND LEVEL, 60 HERTZ (a)			
TRANSFORMER WEIGHT	85 POUNDS			
BOX CATALOG NO. (1)	SB432408 (FLUSH) SB432408S (SURFACE)			
TRIM CATALOG NO. (2)	ST4526 (FLUSH) ST4324 (SURFACE)			

SEISMIC QUALIFICATION:
TO BE COMPLIANT WITH THE SEISMIC REQUIREMENTS OF ASCE/SEI 7.
THIS UNIT HAS BEEN QUALIFIED BY SHAKE TESTING THROUGH SELF CERTIFICATION
TO ICC ES AC156.

- (1) SEPARATE LINE ITEM, ORDER AND SHIP SEPARATE
- (2) SEPARATE LINE ITEM, ORDER AND SHIP SEPARATE, SELECT ONLY ONE.
- (a) MAXIMUM LEAGAGE IN COMPLIANCE OF UL 1047 TABLES 30.1 & 30.2 AND CSA Z32.2

NOTES:
UL LISTED AND CSA
FRONT: BRUSHED STAINLESS STEEL
BOX: PAINTED STEEL OR GALVANIZED STEEL
TRANSFORMER ORDERED AND SHIPPED SEPARATE FOR FIELD INSTALLATION

7.5 kVA ISOLATED POWER PANEL:
INTERIOR, TRANSFORMER, BACKBOX, AND TRIM
(SURFACE OR FLUSH)

Schneider
Electric

DWG# PWEQP-PBSWB-0003
NO.