



NOTES:

1. PLEASE REFER TO PRODUCT MANUALS FOR DETAILS.
- △2. MUST BE L1,L2,L3,N,PE SOURCE PROVIDED BY OTHERS.
3. ----- = AC/DC CABLING PROVIDED BY OTHERS.
4. ALL AC POWER CABLING IS L1,L2,L3,N,PE, UNLESS OTHERWISE SPECIFIED.
- △5. DC CABLING SHOULD BE SEGREGATED FROM AC CABLING SEE BATTERY INSTALLATION INFORMATION.
6. UPS INPUT AND OUTPUT CABLES SHOULD BE SEGREGATED.
7. POWER WIRING AND CONTROL WIRING SHOULD BE SEGREGATED.
- △8. XR BATTERY CABINET IS AVAILABLE WITHOUT BREAKER, WITH DC FUSES ONLY.
9. XR BATTERY CABINET CAN BE BAYED TO UPS. BAYING KIT HAS TO BE PURCHASED AS AN OPTION. UP TO 4 XR BATTERY CABINETS CAN BE CONNECTED TO UPS TO EXTEND BACKUP TIME.
- △10. FOR DUAL MAINS INSTALLATION 3 BRIDGE BUS BARS BETWEEN MAIN AND BYPASS INPUTS HAVE TO BE REMOVED.
- △11. BYPASS INPUT CAN BE PROVIDED VIA MAINS INPUT OR OTHER NON-SYNCHRONIZED SOURCE. PLEASE CONTACT APC IF DUAL SOURCES ARE BOTH SEPARATELY DERIVED POWER SYSTEMS.
12. SUVTP DELIVERED WITH INTERNAL MAINTENANCE BYPASS SWITCH. WHICH NEEDS TO BE REMOVED PRIOR TO CONNECTING FOR PARALLEL OPERATION.
13. OUTPUT OVERCURRENT PROTECTION MUST BE PROVIDED BY OTHERS. RECOMMENDED OUTPUT BREAKER RATING 125A.
- △14. THIS DRAWING SHOWS MAXIMUM NUMBER OF BATTERY MODULES IN EACH CABINET. THE QUANTITY OF BATTERY MODULE IS SKU SPECIFIC.
EX. SUVTPxxKH1B4
 - └─ CAN BE EXPANDED UP TO (4) BATTERY MODULES
 - └─ MINIMUM NUMBER (1) OF BATTERY MODULES.
- EX. SUVTBXR2B6S
 - └─ CAN BE EXPANDED UP TO (6) BATTERY MODULES.
 - └─ MINIMUM NUMBER (2) OF BATTERY MODULES.
15. INSTALLATION MUST COMPLY WITH NATIONAL AND LOCAL ELECTRICAL REGULATIONS.
- △16. MUST BE L1,L2,L3,PE SOURCE PROVIDED BY OTHERS.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: SMART-UPS VT 20kVA
 INPUT: 3x400/230V DUAL MAINS
 OUTPUT: 3x400/230V
 3 MODULE CAPACITY
 SYSTEM ONE LINE DIAGRAM
 PROJECT: SUBMITTAL DRAWINGS SHEET 1 OF 1

DWG NO: SUVTP20KH2C3-SD
 DRAWN: BALAMURUGAN 13-NOV-15
 ENGINEER: SANDERSEN 13-NOV-15
 APPROVED: S.WAGH/E.SILVA 13-NOV-15

REV: 2
 ANGLE PROJECTION: N.A