



DUAL DIMENSIONS: INCHES
MILLIMETERS

SEISMIC QUALIFICATION:
TO BE COMPLIANT WITH THE SEISMIC REQUIREMENTS OF ASCE/SEI 7.
THIS UNIT HAS BEEN QUALIFIED BY SHAKE TESTING THROUGH SELF CERTIFICATION
TO ICC ES AC156.

NOTES:
UL LISTED AND CSA
FRONT: BRUSHED STAINLESS STEEL
BOX: PAINTED STEEL OR GALVANIZED STEEL
TRANSFORMER ORDERED AND SHIPPED SEPARATE FOR FIELD INSTALLATION

	LEFT	RIGHT	LEFT	RIGHT	LEFT	RIGHT	LEFT	RIGHT
PRI V TO SEC V	208 TO 120	208 TO 120	240 TO 120	240 TO 120	277 TO 120	277 TO 120	480 TO 120	480 TO 120
INTERIOR CATALOG NO.	SIX10BA10BAB		SIX10CA10CAB		SIX10DA10DAB		SIX10EA10EAB	
INTERIOR DESCRIPTION	DUPLEX ISOLATION PANEL WITH BARRIER COMPARTMENTS: LEFT 10 KVA, NQ INTERIOR CONTAINING EIGHT 20A 2-POLE BOLT-ON BREAKERS, SPACE FOR EIGHT 2-POLE, I66 LINE ISOLATION MONITOR, GROUND BAR WITH 20 TERMINALS. RIGHT 10 KVA, NQ INTERIOR CONTAINING EIGHT 20A 2-POLE BOLT-ON BREAKERS, SPACE FOR EIGHT 2-POLE, I66 LINE ISOLATION MONITOR, GROUND BAR WITH 20 TERMINALS.							
MAIN CB	QO 60A 2-POLE	QO 60A 2-POLE	QO 60A 2-POLE	QO 60A 2-POLE	HG 45A 2-POLE	HG 45A 2-POLE	HG 30A 2-POLE	HG 30A 2-POLE
TRANSFORMER CAT.NO. REF. NOTE (a)	SXM10BA	SXM10BA	SXM10CA	SXM10CA	SXM10DA	SXM10DA	SXM10EA	SXM10EA
TRANSFORMER WEIGHT	170 POUNDS							
BOX CATALOG NO.	SB71340B (FLUSH) SB71340BS (SURFACE)							
TRIM CATALOG NO.	ST7336 (FLUSH) ST7134 (SURFACE)							

NOTE: ALL CATALOG NUMBERS IN TABLE ABOVE ARE ORDERED AND SHIPPED SEPARATELY.
(a) MAXIMUM LEAGAGE IN COMPLIANCE OF UL 1047 TABLES 30.1 & 30.2 AND CSA Z32.2

DUPLEX PANEL (10 KVA)
INTERIOR, TRANSFORMER, BACKBOX, AND TRIM
(SURFACE OR FLUSH)



DWG# PWEQP-PBSWB-0012
NO.