




END WALL  
CONDUIT ENTRANCE  
TOP & BOTTOM



BOX WITH INTERIOR



BOX SIDE



TYPICAL FRONT

DUAL DIMENSIONS: INCHES  
MILLIMETERS

**SEISMIC QUALIFICATION:**  
TO BE COMPLIANT WITH THE SEISMIC REQUIREMENTS OF ASCE/SEI 7.  
THIS UNIT HAS BEEN QUALIFIED BY SHAKE TESTING THROUGH SELF CERTIFICATION  
TO ICC ES AC156.

	COIL 10KVA	COIL 15KVA	COIL 10KVA	COIL 15KVA	COIL 10KVA	COIL 15KVA
PRI V TO SEC V	208 TO 120	208 TO 208	277 TO 120	277 TO 208	480 TO 120	480 TO 208
INTERIOR CATALOG NO.	SID25BB10BA52		SID25DB10BA52		SID25EB10BA52	
INTERIOR DESCRIPTION	DUAL VOLTAGE ISOLATION PANEL 10KVA: 120 V NQ INTERIOR CONTAINING EIGHT 20 A 2-POLE BOLT-ON BREAKERS, SPACE FOR EIGHT 2-POLE. 15KVA: MAIN CB 208V WITH TWO 50 A 2-POLE BRANCH BREAKERS. (2) IGS LINE ISOLATION MONITOR, GROUND BAR WITH 20 TERMINALS.					
MAIN CB	HG 150A 2-POLE		HG 125A 2-POLE		HG 70A 2-POLE	
SECONDARY CB	QOU100A 2-POLE	QOU80A 2-POLE	QOU100A 2-POLE	QOU80A 2-POLE	QOU100A 2-POLE	QOU80A 2-POLE
TRANSFORMER CAT.NO. REF. NOTE (a)	SXM25BB10		SXM25DB10		SXM25EB10	
TRANSFORMER WEIGHT	370 POUNDS					
BOX CATALOG NO.	SB513414 (FLUSH) SB513414S (SURFACE)					
TRIM CATALOG NO.	ST5336 (FLUSH) ST5134 (SURFACE)					

NOTE: ALL CATALOG NUMBERS IN TABLE ABOVE ARE ORDERED AND SHIPPED SEPARATELY.  
(a) MAXIMUM LEAGAGE IN COMPLIANCE OF UL 1047 TABLES 30.1 & 30.2 AND CSA Z32.2

NOTES:  
UL LISTED AND CSA  
FRONT: BRUSHED STAINLESS STEEL  
BOX: PAINTED STEEL OR GALVANIZED STEEL  
TRANSFORMER ORDERED AND SHIPPED SEPARATE FOR FIELD INSTALLATION

DUAL VOLTAGE PANEL (25 KVA)  
INTERIOR, TRANSFORMER, BACKBOX, AND TRIM  
(SURFACE OR FLUSH)

Schneider  
Electric

DWG# PWEQP-PWSWB-0018  
NO.